



Email : sales@laboratoryinstrumentindia.com

Product Name :
Axial Fan Demonstration Unit

Product Code :
LBNY-0005-103000264



Description :

An axial fan, mounted on a stainless steel plinth. Transparent air inlet and air outlet ducts allow the fan construction to be clearly observed. Electronic sensors measure the pressure head developed across the fan, the pressure across the orifice plate (and hence the flow rate), the rotational speed of the fan and the air temperature. A manually operated adjustable aperture allows the air flow rate to be varied. The fan speed is controlled by modulated dc supply, complete with current sensing to allow the power drawn by the fan to be measured. A calibrated orifice plate is used on the discharge to measure the air flow rate.

A small-scale axial fan demonstration unit, comprising of an inlet duct, the fan, an outlet duct and an adjustable aperture, all mounted on a stainless steel base.

Transparent ducts give visibility of the fan in operation.

Equipped with electronic measurement sensors for fan head pressure, flow-rate (via orifice plate), fan speed and air temperature.

Supplied with software providing full instructions for setting up, operating, calibrating and performing the teaching exercises. Facilities for logging, processing and displaying data graphically.

Full theoretical back-up together with a student questions and answers session.

Capable of being linked to a PC (not supplied) via a dedicated interface console (an essential accessory).

Technical Specification :

Technical Specifications:

Max Head: 0.06 KPa

Max Flow Rate: 38 l/s typical

Motor Power rating 5W

Max fan speed 2700rpm.



Laboratory Instrument India