



Email : sales@laboratoryinstrumentindia.com

Product Name :
Fiber Optic Splicer Electronic Engineering Lab

Product Code :
LBNY-0002-610022



Description :

Fiber Optic Splicer Electronic Engineering Lab

Technical Specification :

Fiber Optic Splicer
Multi-Mode(M M)
Single Mode(SM)
Single Mode(DS/NZDS)Non-Zero Dispersion
Shifted Fiber Cladding diameter: 80...150?m
User Friendly
Touch panel operation with brand-new UI
Smartphone-like easy operation
Long-life battery for 300 splice & heat cycles
High Environment Durability
IPx2 water protection, IP5x dust protection
Work at 6000m, 76cm drop on 5 faces
Compact, Lightweight & Faster
2.2kg with battery for 300 splice & heat cycles
Faster 5s splice in SM Quick Mode
Reduced 9s heat shrink time
Wide and high resolution touch panel
5" touch screen color LCD display
Smartphone-like easy operation

Fiber Optic Splicer Electronic Engineering Lab, Fiber Optic Splicer Electronic Engineering Lab Equipments, Fiber Optic Splicer Electronic Engineering Lab Tools, Fiber Optic Splicer Electronic Engineering Lab Tool Kits, Fiber Optic Splicer Electronic Engineering Lab Manufacturers, Fiber Optic Splicer Electronic Engineering Lab Suppliers from India, China, Kenya



Laboratory Instrument India