



Email : [sales@laboratoryinstrumentindia.com](mailto:sales@laboratoryinstrumentindia.com)

**Product Name :**  
Capacitor Run Motor 60 HZ

**Product Code :**  
LBNY-0005-121000126



[www.laboratoryinstrumentindia.com](http://www.laboratoryinstrumentindia.com)

**Description :**

The capacitor is externally mounted. Specifications and/or diagrams are silk-screened on the back of a clear-plastic front panel for ease of identification. The trainer is protected by either a diode or thermal-magnetic circuit breaker. This trainer is a single-phase unit that can be used to teach the principles of the capacitor-run motor. The main winding, auxiliary winding and the capacitor of the capacitor-run motor are all brought out separately to 4mm terminals on the housing. Included in the Rotating Machines Trainer for 1/3 hp - 250 W. Requires a 120V 60Hz circuit.

**Educational Advantages:**

Equipped with a capacitor that is externally mounted  
Included in the basic Rotating Machines Trainer (50016) for 1/3 hp - 250 Wv  
Single-phase unit that can be used to teach the principles of the capacitor run motor

**Technical Specification :**

Number of machine connections: 6  
Capacitor mounted externally  
Thermal breaker protection  
Power: 120 VAC, 1  
Frequency: 60 Hz  
Speed: 1725 rpm.



**Laboratory Instrument India**