



Email : sales@laboratoryinstrumentindia.com

Product Name :
Workshop Drill Machine

Product Code :
LBNY-0004-730004



Description :

Workshop Drill Machine

Technical Specification :

Drill Machine
Range of Spindle Speed(r.p.m): 65 – 2600
Drilling Speed: 65-2600rpm
Voltage: 220V / 380V / 415V
Max.drilling capacity: 30mm
Spindle travel: 135mm
Spindle speed: 65-2600rpm
Max.distance spindle nose to base: 1100mm
Usage: Metal drilling machine
Power(W): 1100
type: vertical drilling machine
CNC or Not: Normal
Dimension(L*W*H): 1080*620*2150mm
Weight (KG): 450 KG
Spindle taper: MT3
Dimension of base: 400*390mm
Outer Diameter of column: 120mm
Max. tapping capacity: M20
Max. Drilling Dia. (mm): 30 mm

Workshop Drill Machine, Workshop Drill Machine Equipments, Workshop Drill Machine Tools, Workshop Drill Machine Tool Kits, Workshop Drill Machine Manufacturers, Workshop Drill Machine Suppliers from India, China, Kenya



Laboratory Instrument India