



Email : [sales@laboratoryinstrumentindia.com](mailto:sales@laboratoryinstrumentindia.com)

**Product Name :**  
Workshop MAGS (Metal Arc Gas Shielded) Machine

**Product Code :**  
LBNY-0004-740002



**Description :**

Workshop MAGS (Metal Arc Gas Shielded) Machine

**Technical Specification :**

MAGS (Metal Arc Gas Shielded) Machine  
Output Current AC/DC 250 - 275 Amp

**Features:**

- Full Bridge IGBT (Module) inverter technology.
- Continuous adjustment of welding Voltage and current.
- Slow Start facilitates easy arc Striking.
- Reduced melting ball at the end of welding.
- High operating frequency hence small size and weight.
- High power factor & Efficiency.
- compact size and light in weight.

Workshop MAGS (Metal Arc Gas Shielded) Machine, Workshop MAGS (Metal Arc Gas Shielded) Machine Equipments, Workshop MAGS (Metal Arc Gas Shielded) Machine Tools, Workshop MAGS (Metal Arc Gas Shielded) Machine Tool Kits, Workshop MAGS (Metal Arc Gas Shielded) Machine Manufacturers, Workshop MAGS (Metal Arc Gas Shielded) Machine Suppliers from India, China, Kenya



**Laboratory Instrument India**