



Email : sales@laboratoryinstrumentindia.com

Product Name :
Regulator Type ARC Welding Machine

Product Code :
LBNY-0005-1230002



Description :

Welding Current Range: 35-300A 60-400A 80-500A
Welding Voltage Range: 24-32 V 25-38 V 25-40 V
Continuous Hand Welding
Current at 55prct. duty cycle.: 240A 300A 400A
Max Intermittent Current
At 35 prct.duty cycle: 300A 400A 500A
Continuous Voiding Current
at 100 prct. duty codes: 170A 21 OA 260A
Open Circuit Voltage: 65V 75V 75V

Technical Specification :

Electrode sizes Continuous: 6-16G 4-14G 2-14G
Electrode sizes (intermittent): 4G 2G 0G
K.VA (Rated): 15 KVA 21 KVA 25 KVA
Fuse Rating Max at: 400 V 45A 70A 80A
Power Factor Correction
Capacitor: 7 8 10
Input Supply : 2 Lines of 3Phase 415V 50 Hz. AC

Laboratory Instrument India

