



Email : sales@laboratoryinstrumentindia.com

Product Name :
MIG ARC Welder

Product Code :
LBNY-0004-820003



Description :

MIG ARC Welder

Technical Specification :

Specifications

For stainless steel and iron welding, Gas & No Gas self-shielded welding machine

Solid wire/flux cored wire is selectable when doing mig welding'

Capable for 1kg/5kg roll of welding wire' 100% duty cycle can be reached when using 0.8mm wire

Functional machine with MIG, TIG, ARC flinction, maximum welding rod diameter up to 4.0mm

Invetter technology: IGBT

Input voltage: AY220V+15%

FrequencY:5A|60TV

MaxOCV:60V

Duty Cyole: 30%@2A0/'

Powel factor: 0.73

Post flow time: 1.0+0'5

Wire diameter: 0.8/1'0mm

Applicable thickness: Over 0'8mm

Wire feed sPeed: 3^18rn/min

Accessory

Mig torch

Electrode holder

Earth clamp
Gas tube
Flux cored wire 1kg 20Ea
Pack of tips and nozzles
Lift torch(17V")
Welding Mask.



Laboratory Instrument India