



Email : sales@laboratoryinstrumentindia.com

**Product Name :**  
AC and DC Arc Welder

**Product Code :**  
LBNY-0004-820057



**Description :**

AC and DC Arc Welder

**Technical Specification :**

AC and DC Arc Welder

Specifications:

Full Digital Arc Welding Machine,  
Interface design through LCD and encoder

MMA welding

AC ARC Welding: Yes

DC ARC Welding: Yes

DCRP(-) function is DCARC welding where the base material is negative polarity

DCSP(+) function is welding where the base material is positive polarity

Current control of welding machine is possible using mobile phone application

Rated input power (ACV): 220V, 50L12

Rated input (KVA): 11.5

Rated Power (KW): 9.6

Rated load voltage (V): 32

High Utilization Current (A): 230-250

Rated utilization load voltage (V): 29

Output current regulation range (A): 30-300

Output voltage range (V): 22-32

Accessory

---

Welding wire (3M) 1 Ea  
Holder clamp(300A) 1 Ea  
Earth wire(3M) 1 Ea  
Earth tongs (300A) 1 Ea  
Covered Arc welding rod(2.6) 5KG, 10Ea  
CoveredAlc welding rod(3,2) 5KG, 10Ea  
Welding Mask



**Laboratory Instrument India**