



Email : sales@laboratoryinstrumentindia.com

**Product Name :**

Ambulance, 4 door w/1 sliding side door, back door lift-up type, 7-seater, 2.4 L diesel engine

**Product Code :**

LBNY-0026-220011



**Description :**

Standard specification for the Ambulance:

Main stretcher with caster

Room lamp, 1 pc

Attendant seat, 5 persons

Electric Siren Amplifier & Speaker, 1 tone

Fire extinguisher

Beacon lamp, red

Floor, plywood & linoleum covered floor.

Standard Equipment:

Air cleaner, cyclone type

Clock, built-in trip meter

Electrical system, 12V

Fire extinguisher, 1kg install

Front headrests, 3pcs for LHD, 2pcs for RHD

Air conditioner, front and rear (Non CFC)

Assist grips, front:3

Battery, 85D26Rx2(55AHx2)

Beacon lamp(red, front 55W)

Cigarette lighter

Head lamp, sculptured 2

Heater, front & rear

Inside rear view mirror, day and night  
Intermittent wiper, intermittent  
Front seat: 3persons  
Front seat belt, 3P ELRx2 + NRx1  
Front wheel brake, disc (15 inches)  
Fuel lid opener, cable type  
Plywood & linoleum covered floor  
Power steering  
Pre-air cleaner  
Radio, AM/FM, w/ 2 sp.  
Lockable fuel tank  
Main stretcher w/ caster  
Mud guards, w/o  
Outside rear view mirror, 2pcs  
Rear door inside handle  
Rear seat, w/o  
Rear wheel brake, drum  
Room lamp(8W) : front + center + rear  
Seat material, fabric  
Steering wheel, 2-spoke urethane  
Sub stretcher, folding  
Sun visors, 2 pcs.  
Suspension, fr:double wishborn, rr:rigid leaf  
Tool kit with jack & Jack handle  
Touch-up paint  
Seats, attendant, folding type, 4 persons  
Side door beam, front and slide door  
Siren amplifier, electric & speaker (1 tone type)  
Spare wheel, 1pc (full size)  
Steering column, manual tilt  
Towing eye, front and rear  
Wheel cap, full cap  
Wheel house cover  
Towing hook, fr: 1  
Transport hook, fr: 2  
Triangle caution plate, 1pc loaded  
Tyres: 195R15C 8PR Tubeless 15x6JJ  
Windshield glass, green (adhesion).

**Technical Specification :**

Brakes and Tyres:  
Brakes Front: Disc  
Brakes Rear: Drum  
Tube: No  
Alternator: 120  
Battery: 60 Ah  
Tyres Front: 195R15C 8PR  
Tyres Rear: 195R15C 8PR

Engine Information:  
Mount: Front Longitudal  
Displacement: 2986  
Assembly: OHC

---

Power: 68 kw at 4000 rpm  
Torque: 197 Nm at 2400 rpm  
Cylinders: 4  
Valves per cylinder: 2  
Formation: In-line  
Turbo: N/A  
Emission control: N/A  
Fuel tank capacity: 70 L  
Fuel type: Diesel  
Fuel injection: EFI.



**Laboratory Instrument India**