



Email : sales@laboratoryinstrumentindia.com

Product Name :
Hi-Vis Class II Vests

Product Code :
LBNY-00017-11000855



Description :

Mesh vest has zipper closure; solid vest available with zipper or hook-and-loop closure
2 in. Level 2 ANSI-compliant tape
One inside pocket
Two outside pockets
Expandable Vest 8240HL
Made of ANSI-compliant polyester mesh (3.3 oz.)
High visibility, glowing vests keep workers safe on the job
Economy Vests 8210HL
Made of mesh (3.3 oz.)
2 in. (5.1cm) Level 2 ANSI-compliant tape
One inside pocket
Available with hook and loop closure
Hook and loop closure
Two-Tone Vest 8230Z
Made of ANSI-compliant polyester (3.3 oz.)
2 in. Level 2 ANSI-compliant tape
One inside pocket
Level 2 ANSI-compliant tape
Tape set on 4.5 in. (11.4cm) contrasting color background
Radio tabs/holders
One multi-division inside pocket
Zipper closure
Made of polyester mesh (2.6 oz.)

Hook and loop closure
1 in. (2.54cm) reflective tape.
Tape set on 4.5 in. (11.4cm) contrasting color background.

Technical Specification :

Hi-Vis Class II Vests



Laboratory Instrument India