



Email : sales@laboratoryinstrumentindia.com

Product Name :
Sheet Metal Ductility Testing Machine With Ball Screw
FPGA Test Equipment

Product Code :
LBNY-0005-1460001



Description :

Use ball screw, high accuracy
High coaxial degree.
Can set the depth and load
Special differential circuit, power and peripheral interface full isolation design, anti-interference ability
Through the special differential circuit with FPGA internal pure hardware high precision digital displacement device makes test results more accurate and reliable;
FPGA, Single Chip and with 100 m data processing speed to make sure data wont be missed
Collecting and processing data at the same time, Control stability efficient
7 inch TFT industry true color touch display, graphics beautiful, operating more humanization;
Electrical design satisfy EMC safety standards
Two way and a high precision AD collection, stamping load and clamping force is more exquisite, limit position protection, full scale overload protection function.

Technical Specification :

Sheet Metal Ductility Testing Machine With Ball Screw FPGA Test Equipment

Laboratory Instrument India

